

Product sheet



LEGRAND

Bell - for industrial and alarm use - IP40 - IK08 230 V~
- Ø100 mm gong

REF. 041349 | EAN. 3245060413491

> [Visit e-catalogue](#)

Product characteristics

- Bells for industrial and alarm use
- Class I - Double insulated - Polyester corrosion resistant finish - 200 hours maxi. continuous rating IP 40 - IK 08 - 50/60 Hz - Alternating current version - 100 mm gong - RAL 7037 Grey - Voltage : 230 V~ - Consumption : 50 mA - Average acoustic output at 1 m : 95 dB - Weight : 0,8 kg

Documentation

TECHNICAL DOCUMENTATION

 LE14377AA.pdf | PDF (0.46Mo)

Agreements & Certificates

 LGRP-00143-V01.01-EN.pdf | PDF (0.61Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0551.pdf | PDF (0.1Mo)