

CAT. N° 0 784 52



180° SWITCH SENSOR MOSAIC - 15 M² - DUAL-TECH - VACANCY MODULES WITH NEUTRAL - WHITE

Pack (number of units)	1
Volume (dm ³)	0,237
Weight (g)	87,00

Product characteristics

3-wire presence sensor, with neutral

- Infrared and ultrasonic double technology
- Allows a precise presence detection. Checks the light level continuously and not only at the time of detection
- Propose a special mode: manual switching on with integrated pushbutton, automatic switching off
- Accepted power by lamp type:
 - LEDs: 0 to 250 W
 - Compact fluorescent: 0 to 250 W
 - LEDs, CFLs, Halogen, fluo tubes with ferromagnetic or electronic transformer: 0 to 1000 VA
 - Halogen 230 V, incandescent: 0 to 2000 W
- Up to 10 sensors can be connected in parallel
- Additional remote manual control possible with push button
- Time delay setting from 5 s to 30 min
- Light level threshold setting from 5 lux to 1275 lux
- Standby consumption : 0.4 W
- Mosaic
- With neutral

General characteristics

Mosaic™ Programme mechanisms - motion and presence sensors

- All sensors are compatible with any lamp - Detection field: 120°
- Detection range: 8 m
- Recommended installation height: 1.20 m
- Integrated self-protection against overloads and short-circuits.
- 2 modules

Documentation

Catalogue pages & additional information

- [Selection chart \(p.659\)](#)
- [Description page \(p.664\)](#)
- [Description page \(p.880\)](#)
- [Technical page \(p.882\)](#)
- [Motion sensors and Lighting Management sensors for controllers](#)
- [Lighting management stand-alone sensors](#)

Installation & technical data

- [S000066736EN-1](#)
- [LE06321AD_EN](#)

Installation instructions & related documents

- [LE04391AA](#)

Agreements & certificates of conformity

- [OC / CB - 645761D](#)