

CAT. N° 4 460 83



19" CABLING CABINET LCS³ - CAPACITY 37U - WIDTH 800 MM , DEPTH 1000 MM AND HEIGHT 1800 MM

Pack (number of units)	1
Volume (dm ³)	1824,768
Weight (g)	126 800,00

Product characteristics

19" cabling cabinets – 800 mm wide

- Suitable for use with patching, network and server equipment
- Stand-alone racks come with (removable) side panels
- Specifications:
 - frame: aluminium, demountable
 - supplied with a 25 mm or 100 mm plinth
 - load capacity: 1500 kg (static)
 - base size: 800 mm wide
- Doors (800 and 1000 mm racks):
 - (clear) glass front door, metal back door
 - right-hinged and fitted with a Fix-easy swivel handle with an EK-333 cylinder lock
- Roof: 3 or 4 cut-outs with 2 or 3 blind plates and 1 cable entry brush, depending on the frame size
- Interior: rack equipped with 4 x 19" profiles including height (U) indication. Distance to the rack front: set to 175 mm (pitch set to 740 mm). In case of racks depth 800 mm, distance to the back set to 87.5 mm (pitch set to 537.5 mm)
- Racks supplied with 20 cage nuts and screws
- Capacity : 37 U
- Width : 800 mm
- Depth : 1000 mm
- Height : 1800 mm

General characteristics

Legrand cabling system LCS³ enclosures - cabling cabinets and accessories

Documentation



Catalogue pages & additional information

- [Selection chart \(p.59\)](#)
- [Description page \(p.100\)](#)
- [Technical page \(p.111\)](#)



Installation & technical data

- [Datasheet LSC3 cabling cabinet](#)