

CAT. N° 7 521 58



2-GANG TWO-WAY SWITCH VALENA LIFE - 10 AX 250 V~ - IP44 - WHITE

Pack (number of units)	5
Volume (dm ³)	2,668
Weight (g)	477,00

Product characteristics

Switches 10 AX- 250 V~

- Automatic terminals

2-gang two-way switch

- White

General characteristics

Valena™ Life - IP44 devices with white cover plate

- Valena In'Matic mechanisms supplied with white cover plates, weatherproof membrane and support frames
- To be equipped with plates
- Supplied with mounted dust protection transparent shield
- Flowpack packaging: robust protection to ensure optimum operation

Documentation

Catalogue pages & additional information

- [Description page \(p.525\)](#)

Installation & technical data

- [F02085EN/00](#)

Installation instructions & related documents

- [LE08107AA](#)

Agreements & certificates of conformity

- [NF - NF012_1596](#)
- [VDE - 40044639](#)
- [OC / CB - FR_703340](#)