

CAT. N° 0 504 90



## 2P+E MULTI-SOCKET PLUG -GERMAN STANDARD -2 FRONT OUTLETS -IK08 -BLACK -GENCOD LABEL

Pack (number of units)	4
Volume (dm <sup>3</sup> )	3,172
Weight (g)	607,00

### Product characteristics

#### 2P+E multi-socket plugs - 16 A

- Max. admissible power 3.680 W at 230 V~

#### 2 front outlets - shockproof IK 0

- Gencod labelling
- Rubber multi-socket plug with caps - IP 44
- Black

### General characteristics

#### Multi-socket plugs and extensions - German standard

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.637\)](#)



#### Agreements & certificates of conformity

- [MEEI - UP 69257701 0001](#)
- [OC / CB - 693649](#)