

CAT. N° 7 530 24



## 2P+E SOCKET WITH SHUTTERS VALENA IN'MATIC -SCREW TERMINALS -GERMAN STANDARD-16 A-250 V~

Pack (number of units)	10
Volume (dm <sup>3</sup> )	3,802
Weight (g)	82,00

### Product characteristics

#### German standard socket outlets 16 A - 250 V~

##### 2P+E sockets with shutters

- Screw terminals
- Illuminated version with LED Cat.No 0 676 64
- Specific cover for illuminated version, Life and Allure

### General characteristics

#### Valena™ IN'MATIC mechanisms - socket outlets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- IP 2X protection
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.502\)](#)
- [Selection chart \(p.511\)](#)
- [Selection chart \(p.515\)](#)



#### Agreements & certificates of conformity

- [MEEI - UP 69248331 0001, 0002, 0003](#)
- [OC / CB - HU-001410](#)
- [OC / CB - HU-001784](#)



#### Installation & technical data

- [F01949EN-00](#)