

CAT. N° 0 778 41



2-WAY PUSH-BUTTON SOLIROC - 6 A 230 V~ - IP55 - NO-NC CONTACT

Pack (number of units)	1
Volume (dm ³)	0,68
Weight (g)	177,00

Product characteristics

Push-buttons 6 A - 230 V~ - IK 10 - IP 55

- Two-way push-button
- NO-NC contact

General characteristics

Soliroc™ - control mechanisms IK 10

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied with cover plates, to be equipped with support frames and plates

Documentation

Catalogue pages & additional information

- [Description page \(p.610\)](#)

Agreements & certificates of conformity

- [NF - NF012_1023](#)
- [QC / CB - FR_707077](#)

Installation & technical data

- [F00997EN-04](#)