

CAT. N° 0 778 11


2-WAY SWITCH SOLIROC - 10 AX 250 V~ - IP55


Pack (number of units)	1
Volume (dm ³)	0,68
Weight (g)	192,00

Product characteristics
Switches 10 AX - 250 V~

- 2-way switch

General characteristics
Soliroc™ - control mechanisms IK 10

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied with cover plates, to be equipped with support frames and plates

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.610\)](#)

 **Agreements & certificates of conformity**

- [NF - NF012_1023](#)
- [OC / CB - FR_707077](#)

 **Installation & technical data**

- [F00997EN-04](#)

 **Environmental product profile**

- [Environnemental product sheet n°A E2453A-FR](#)