

REF . 7 520 10



## 2-WAY SWITCH WITH NEUTRAL VALENA IN'MATIC - 10 AX 250 V~



Emballage (nombre number of units )	5
Volume (dm <sup>3</sup> )	1,912
Poids (g)	387,00

### Caractéristiques du produit

#### Switches 10 AX - 250 V~

##### Two-way switch with neutral terminal

- Automatic terminals
- Becomes illuminated with LED Cat.No 0 676 86 or 7 520 57 (surround lighting in Valena Allure range)
- Indicator version: with LED Cat.No 0 676 88 or 7 520 58 (surround lighting in Valena Allure range)
- Possibility to wire a lamp (locator or indicator version) between the phase and the neutral terminals, to avoid the "ghost effect"

### Caractéristiques générales

#### Valena™ IN'MATIC mechanisms - switches

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- Supplied with mounted dust protection transparent shield
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Packaged in boxes

### Documentation associée



#### Catalogue pages & additional information

- [Description page \(p.494\)](#)
- [Selection chart \(p.508\)](#)
- [Selection chart \(p.512\)](#)



#### Installation & technical data

- [F02081FR/00](#)
- [F02081EN/00](#)



#### Installation instructions & related documents

- [LE09162AD](#)



#### Agreements & certificates of conformity

- [NF - NF012\\_1596](#)
- [OC / CB - FR\\_703340](#)