

CAT. N° 2 839 23



2X2P+E MULTISTANDARD SOCKET OUTLET WITH USB CHARGER MALLIA - 16 A-250 V / 15 A-127 V - 2 GANG - CHAMPAGNE

Pack (number of units)	1.0000
Volume (dm ³)	0,729
Weight (g)	202,00

Product characteristics

Multistandard switched socket outlets 16 A - 250 V~ / 15 A - 127 V~ with USB charger

- USB charger conform to IEC 60950-1
- Supplied complete with plates

2 x 2P+E - 2 gang

- USB Type-A + Type-C™ 3 A - 5 VDC - 15 W
- Consumption in passive mode less than 0.08 W
- Champagne

General characteristics

Mallia™ - multistandard and US standard socket outlets - customisable colours

- Painted polycarbonate front cover
- Compact mechanism for greater wiring space
- Supplied with 2 screws M 3.5 for BS boxes
- All sockets integrate child protection
- Dim.: 86 x 86 mm

Documentation



Catalogue pages & additional information

- [Description page \(p.574\)](#)



Installation & technical data

- [F02765EN/00](#)