

CAT. N° 8 330 09



3 POLE FAN SWITCH SYNERGY - 10 A 250 V~ - AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	154,00

Product characteristics

3 pole fan switches 10 A - 250 V~

- Conform to BS EN 60669-1: 2000
- With integrated padlockable safety block in OFF position
- Flush mounting back box: min. 25 mm deep
- Nominal plate dimensions: 86 x 86 mm
- Brushed stainless steel

General characteristics

Synergy™ - fan switch and double pole switches - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation



Catalogue pages & additional information

- [Description page \(p.586\)](#)



Installation & technical data

- [F02319EN-00](#)