

CAT. N° 0 489 44



## 360° MOTION SENSOR - IP41 - 8 M - FLUSH CEILING-MOUNTING - PIR TECHNOLOGY - BLISTER

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,093
Weight (g)	123,00

### Product characteristics

#### Ideal for passage areas

#### PIR IP 20 ceiling-mounting motion sensor, 360°

- Blister
- Range Ø8 m
- Recommended fixing height: 2.5 m
- 3-wire with neutral
- Light level threshold: 10 to 1275 lux
- Adjustable time delay: 10 s to 10 min
- Standby consumption: 0.75 W
- Optimum distance between 2 sensors: 6 m
- Fixes directly to a false ceiling with mounting claws (included) or installed in a Batibox box, depth 50 mm

### General characteristics

#### Motion sensors for 1 circuit - motion sensors for passage areas without natural light

- Automatic on/off
- Manual adjustment of light level threshold and time delay via potentiometer

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.658\)](#)
- [Description page \(p.661\)](#)
- [Technical page \(p.662\)](#)
- [Motion sensors and Lighting Management sensors for controllers](#)

#### Installation & technical data

- [S000087115EN-2](#)

#### Environmental product profile

- [Environnemental product sheet n°A E0164A-EN](#)

#### Installation instructions & related documents

- [LE07906AC](#)

#### Agreements & certificates of conformity

- [OC / CB - 685326](#)