

CAT. N° 4 105 11


**ADD-ON MODULES DX³ - 4P 400 V~ - 40 A - 300 MA - AC
TYPE - FOR 1 MODULE DX³ MCB**


Pack (number of units)	1
Volume (dm ³)	1,684
Weight (g)	307,00

Product characteristics
4-pole - 400 V~
AC Type

- Sensitivity : 300 mA
- Nominal rating I_n : 40 A
- Number of modules : 3

General characteristics
Add-on modules DX³ - for 1 module/pole DX³ MCBs

- Conform to IEC 61009-1, IEC 62423 (F type)
- Voltage independent tripping except Cat.No 4 106 57/58/59
- AC type : detect AC components faults
- A type : detect AC and DC component faults
- F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping
- Detection of high frequency fault currents
- For mounting on the right-hand side of 1 module per pole DX³ MCBs

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.070\)](#)
- [Technical page \(p.071\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Installation & technical data**

- F01305EN/05

 **Environmental product profile**

- [Environnemental product sheet n°20 E0113A-FR](#)

 **Installation instructions & related documents**

- [LE03772AC](#)

 **Agreements & certificates of conformity**

- NF - NF012_1340
- OC / CB - IT-11142
- CCC - 2016010307899559