

CAT. N° 0 280 18

**AIR CIRCUIT BREAKER DMX<sup>3</sup> 1600 LCU 42 KA - DRAW-OUT VERSION - 4P - 630 A**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	107,653
Weight (g)	56 412,00

**Product characteristics****Draw-out version**

- Supplied with
  - 4 auxiliary contacts: NO/NC
  - draw-out base and kit
  - rear orientable terminals for horizontal and vertical connection with bars
  - door sealing

**Breaking capacity Icu 42 kA (415 V~)**

- Frame 1600
- 4P
- In : 630 A

**General characteristics****Air circuit breakers DMX<sup>3</sup> 1600 - from 630 to 1600 A**

- Automatic air circuit breakers must be equipped with DMX<sup>3</sup> 1600 electronic protection units Cat.No 0 281 64/65/66, imperatively ordered together for factory assembly
- Please ask for DMX<sup>3</sup> order form
- Conform to IEC 60947-2

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.156\)](#)
- [DMX3 1600 and DMX3-I 1600 - Frame 1600](#)
- [DMX3 1600 electronic protection units](#)

 **Installation & technical data**

- [LE10707AA](#)

 **Installation instructions & related documents**

- [LE08437AC](#)