

REF . 0 280 08

**AIR CIRCUIT BREAKER DMX³ 1600 LCU 42 KA - FIXED VERSION - 4P - 1000 A**

Emballage (nombre number of units)	1
Volume (dm ³)	107,653
Poids (g)	29 712,00

Caractéristiques du produit**Fixed version**


- Supplied with
- 4 auxiliary contacts: NO/NC
- rear orientable terminals for horizontal and vertical connection with bars
- door sealing

Breaking capacity Icu 42 kA (415 V~)

- Frame 1600
- 4P
- In : 1000 A

Caractéristiques générales**Air circuit breakers DMX³ 1600 - from 630 to 1600 A**

- Automatic air circuit breakers must be equipped with DMX³ 1600 electronic protection units Cat.No 0 281 64/65/66, imperatively ordered together for factory assembly
- Please ask for DMX³ order form
- Conform to IEC 60947-2

Documentation associée **Catalogue pages & additional information**

- [Description page \(p.156\)](#)
- [DMX3 1600 and DMX3-I 1600 - Frame 1600](#)
- [DMX3 1600 electronic protection units](#)

 **Installation & technical data**

- [F02194EN/04](#)
- [LE10707AA](#)

 **Installation instructions & related documents**

- [LE08437AC](#)