

CAT. N° 0 286 72



AIR CIRCUIT BREAKER DMX³ 2500 LCU 100 KA - FIXED VERSION - 4P - 1000 A

Pack (number of units)	1
Volume (dm ³)	298,584
Weight (g)	97 500,00

Product characteristics

Fixed version

- Supplied with
 - 4 auxiliary contacts: NO/NC
 - rear terminals for horizontal connection with bars
 - door sealing

DMX³ - L 2500

- Breaking capacity Icu 100 kA (415 V~)
- Frame 4000
- 4P
- In : 1000 A

General characteristics

Air circuit breakers DMX³ 2500 and 4000 - from 800 to 4000 A

- Automatic air circuit breakers must be equipped with electronic protection unit, imperatively ordered together for factory assembly
- Please ask for DMX³ order form
- Conform to IEC 60947-2

Documentation

Catalogue pages & additional information

- [Description page \(p.160\)](#)
- [DMX3 - frame 2500, 4000 & 6300](#)
- [DMX3 - electronic protection units](#)

Installation & technical data

- [Y2687H](#)
- [F01800EN/01](#)
- [Y2958H](#)

Installation instructions & related documents

- [Y2762C](#)