

CAT. N° SL532190


**ASTREO LED ROUND DECORATIVE BULKHEAD LIGHT -
IP44 - IK09 VANDAL-RESISTANT - EQUIPPED - 800 LM -
ON/OFF**

| | |
|---------------------------|--------|
| Pack (number of units) | O/R |
| Volume (dm ³) | 11,476 |
| Weight (g) | 800,00 |

Product characteristics
**IP 44 - IK 07/09 LED round decorative bulkhead lights -
equipped**

- Ø330 mm
- 4000 K – IRC 80
- Life time: 40,000 hours
- Polycarbonate base and opal diffuser with captive screws
- Screwless connection terminals

Astreo IK 09 vandal-resistant bulkhead lights

- 800 lm – On/Off

General characteristics
IP 44/54/55 weatherproof bulkhead lights
Documentation

Catalogue pages & additional information

- [Description page \(p.676\)](#)
- [Weatherproof bulkhead lights](#)


Installation instructions & related documents

- [LE09749AD](#)