

CAT. N° 0 577 20

**BASE UP TO 3 SOCKETS FOR COMBINED UNIT P17 - 16 A - 421 X 125 MM**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	11
Weight (g)	778,00

**Product characteristics****Combined units height 280 mm to 501 mm****Base for 280 x 125 mm faceplates - max. IP 66**

- Base up to 3 sockets 16 A
- Rail 5 modules 17.5 mm
- External dimensions (Height x Width) : 421 x 125 mm

**General characteristics****P17 Tempra combined units to be composed**

- IK 08 according to IEC 62262
- Self-extinguishing: 650 °C
- Max. IP 66

**Documentation****Catalogue pages & additional information**

- [Selection chart \(p.386-387\)](#)
- [Technical page \(p.388\)](#)

**Installation & technical data**

- [F00140EN-05](#)