

CAT. N° 0 413 49



## BELL - FOR INDUSTRIAL AND ALARM USE - IP40 - IK08 230 V~ - Ø100 MM GONG

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,932
Weight (g)	508,00

### Product characteristics

#### Class I

- Double insulated
- Polyester corrosion resistant finish
- 200 hours maxi. continuous rating

#### IP 40 - IK 08 - 50/60 Hz - Alternating current version

- Ø 100 mm gong
- RAL 7037 Grey
- Voltage : 230 V~
- Consumption : 50 mA
- Average acoustic output at 1 m : 95 dB
- Weight : 0.8 kg

### General characteristics

#### Bells for industrial and alarm use

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.394\)](#)



#### Environmental product profile

- [Environnemental product sheet n°4 E0063A-EN](#)



#### Installation instructions & related documents

- [4065604/01](#)