

CAT. N° 6 170 57

**BRITISH STANDARD SOCKET OUTLET BELANKO WITH
USB TYPE A CHARGER - 1 GANG UNSWITCHED - 13 A 250
V~**

Pack (number of units)	1
Volume (dm ³)	0,426
Weight (g)	122,00

Product characteristics**British Standard socket outlets - 13 A- 250 V~ with USB
charger**

- Conform to BS 1363-2:2016
- Conform to IEC 60950-1

1 gang

- USB Type-A 2.4 A - 5 VDC - 12 W
- Consumption in passive mode less than 0.08 W
- 1 gang unswitched

General characteristics**Belanko™ - socket outlets**

- Colour: White T084
- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

Documentation**Catalogue pages & additional information**

- [Description page \(p.551\)](#)

**Agreements & certificates of conformity**

- [OC / CB - SE-86036](#)
- [OC / CB - SE-86036M1](#)

**Installation & technical data**

- [F02764EN-00](#)