

CAT. N° 8 322 59



## BRITISH STANDARD SYNERGY -1 GANG UNSWITCHED -2 A -250 V~ SLEEK DESIGN POLISHED STAINLESS STEEL

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Socket outlets 2 A - 250 V~

- Conform to BS 546
- For flush-mounting, back box to be min. 25 mm deep
- Nominal plate dimensions: 86 x 86 mm

#### 1 gang unswitched

- Polished stainless steel

### General characteristics

#### Synergy™ - British standard socket outlets and USB sockets - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.592\)](#)



#### Installation & technical data

- [F02277EN/00](#)