

CAT. N° 8 322 61



## BRITISH STANDARD SYNERGY -DOUBLE POLE 1 GANG SWITCH + LED -13 A -250 V~ SLEEK DESIGN POLISHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	169,00

### Product characteristics

#### Double pole socket outlets 13 A - 250 V~

- Conform to BS EN 1363: Part. 2
- With safety shutter mechanism
- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm (1 gang), 86 x 146 mm (2 gang)
- ASTA licence

#### 1 gang switched with blue LED power indicator

- Polished stainless steel

### General characteristics

#### Synergy™ - British standard socket outlets and USB sockets - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.592\)](#)

#### Agreements & certificates of conformity

- [ASTA - 780](#)

#### Installation & technical data

- [F02264EN/00](#)