

CAT. N° 8 320 71



BRITISH STANDARD SYNERGY -DOUBLE POLE 2 GANG SWITCH + LED -13 A -250 V~ SLEEK DESIGN BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,769
Weight (g)	270,00

Product characteristics

Double pole socket outlets 13 A - 250 V~

- Conform to BS EN 1363: Part. 2
- With safety shutter mechanism
- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm (1 gang), 86 x 146 mm (2 gang)
- ASTA licence

2 gang switched with blue LED power indicator

- Brushed stainless steel

General characteristics

Synergy™ - British standard socket outlets and USB sockets - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.592\)](#)

Agreements & certificates of conformity

- [ASTA - 780](#)

Installation & technical data

- [F02264EN/00](#)