

CAT. N° 0 362 05



CABLE DUCTING LINA 25 - WIDTH 40 X HEIGHT 25 MM - BLUE 2525 - L. 2 M

Pack (number of metres)	56
Volume (dm ³)	53,434
Weight (g)	22 600,00

Product characteristics

Lina 25 ducting

- RAL 2525 blue PVC
- Conform to EN 50085-2-3
- 6.5 mm wide fingers with a 6 mm spacing
- Accepts up to 6 mm² without breaking side wall fingers
- Two pre-scored lines allow removal of fingers
- Bump on side wall fingers help cabling
- Rounded fingers prevent injury during cabling
- Conform to EN 50085 parts 2 and 3
- Plastic cable ducting (base + cover)
- Side perforations at intervals of 12.5 mm. Length: 2 m
- Width x height : 40 x 25 mm

General characteristics

Lina 25™ cable ducting

Documentation

Catalogue pages & additional information

- [Description page \(p.348\)](#)
- [Technical page \(p.349\)](#)

Agreements & certificates of conformity

- [NF 004 - 641237C](#)
- [UL recogn - E212478](#)
- [CSA - 700861](#)

Installation & technical data

- [F01892EN-00](#)