

REF . 0 980 08

**CABLE GLAND PLASTIC - IP68 - ISO 50 - CLAMPING CAPACITY 30-38 MM - RAL 7001**

Emballage (nombre number of units)	2
Volume (dm ³)	1,409
Poids (g)	256,00

Caractéristiques du produit**Grey RAL 7001 cable glands**

- Anti-vibration mechanically tightened cable gland with neoprene weatherproof seal for IP 68 protection
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal and locking nut mounted

ISO

- Conform to EN 50 262
- ISO : 50
- Clamping capacity Ø Min. : 30 mm
- Clamping capacity Ø Max. : 38 mm

Caractéristiques générales**Plastic cable glands IP 68 - ISO and PG****Documentation associée****Catalogue pages & additional information**

- [Description page \(p.316\)](#)