

CAT. N° 0 980 23

**CABLE GLAND PLASTIC - IP68 - PG 13.5 - CLAMPING CAPACITY 6-12 MM - RAL 7001**

Pack (number of units)	25
Volume (dm ³)	1,409
Weight (g)	357,00

Product characteristics**Grey RAL 7001 cable glands**

- Anti-vibration mechanically tightened cable gland with neoprene weatherproof seal for IP 68 protection
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal and locking nut mounted

PG

- Conform to UTE C 68-300 and 68-311 guides recommendations
- PG : 13.5
- Clamping capacity Ø Min. : 6 mm
- Clamping capacity Ø Max. : 12 mm

General characteristics**Plastic cable glands IP 68 - ISO and PG****Documentation****Catalogue pages & additional information**

- [Description page \(p.316\)](#)