

REF . 0 980 26

**CABLE GLAND PLASTIC - IP68 - PG 29 - CLAMPING CAPACITY 18-25 MM - RAL 7001**

|                                     |        |
|-------------------------------------|--------|
| Emballage (nombre number of units ) | 5      |
| Volume (dm <sup>3</sup> )           | 1,409  |
| Poids (g)                           | 266,00 |

**Caractéristiques du produit****Grey RAL 7001 cable glands**

- Anti-vibration mechanically tightened cable gland with neoprene weatherproof seal for IP 68 protection
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal and locking nut mounted

**PG**

- Conform to UTE C 68-300 and 68-311 guides recommendations
- PG : 29
- Clamping capacity Ø Min. : 18 mm
- Clamping capacity Ø Max. : 25 mm

**Caractéristiques générales****Plastic cable glands IP 68 - ISO and PG****Documentation associée****Catalogue pages & additional information**

- [Description page \(p.316\)](#)