

CAT. N° 0 980 29



CABLE GLAND PLASTIC - IP68 - PG 48 - CLAMPING CAPACITY 34-44 MM - RAL 7001

Pack (number of units)	2
Volume (dm ³)	1,409
Weight (g)	305,00

Product characteristics

Grey RAL 7001 cable glands

- Anti-vibration mechanically tightened cable gland with neoprene weatherproof seal for IP 68 protection
- Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength
- Supplied with surface seal and locking nut mounted

PG

- Conform to UTE C 68-300 and 68-311 guides recommendations
- PG : 48
- Clamping capacity Ø Min. : 34 mm
- Clamping capacity Ø Max. : 44 mm

General characteristics

Plastic cable glands IP 68 - ISO and PG

Documentation



Catalogue pages & additional information

- [Description page \(p.316\)](#)