

CAT. N° 0 262 70



## CAGE TERMINALS (4) - FOR DPX 1600 - RIGID CABLE 4X240 MM<sup>2</sup> / 4X185 MM<sup>2</sup> FLEXIBLE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,315
Weight (g)	734,00

### Product characteristics

#### Accessories

##### Cage terminals

- Set of 1 high-capacity terminal for cables without lug
- 4 x 240 mm<sup>2</sup> for rigid cable
- 4 x 185 mm<sup>2</sup> for flexible cable

### General characteristics

#### DPX™-IS 1600 isolating switches - 800 to 1600 A

- Isolating switches for on-load circuit breaking by visible isolation and positive action of the contacts
- Connection with cage terminals
- Padlock integrated in the handle
- Supplied with terminal shields
- Conform to IEC 60947-3
- Category of use AC 23 A
- Accept electrical auxiliaries
- Can be mounted on plate in XL<sup>3</sup> enclosures

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.153\)](#)
- [Description page \(p.169\)](#)
- [Technical page \(p.170\)](#)
- [DPX<sup>3</sup> 1600](#)
- [DPXTM-IS 1600 isolating switches](#)