

CAT. N° 0 374 19

COPPER BAR - FLAT RIGID - SECTION 32 X 5 MM - 400 TO 450 A - L. 1750 MM



| | |
|---------------------------|----------|
| Pack (number of units) | 4 |
| Volume (dm ³) | 1 |
| Weight (g) | 9 300,00 |

Product characteristics
Copper bars
Rigid, flat, threaded holes

- Cross section : 32 x 5 mm
- I permissible IP ≤ 30 : 450 A
- I permissible IP > 30 : 400 A
- Holes Ø mm : M6
- Length : 1750 mm

General characteristics
Copper bars and accessories

- Standard distribution

Documentation
 **Catalogue pages & additional information**

- [Selection chart \(p.260-261\)](#)
- [Description page \(p.260-261\)](#)
- [Selection chart \(p.282-283\)](#)
- [Description page \(p.282-283\)](#)