

CAT. N° 8 332 52



## CORD OUTLET SYNERGY - 1 GANG - AUTHENTIC POLISHED STAINLESS STEEL

|                           |     |
|---------------------------|-----|
| Pack (number of units)    | O/R |
| Volume (dm <sup>3</sup> ) | O/R |
| Weight (g)                | O/R |

### Product characteristics

#### Cord outlets

##### 1 gang

- Nominal plate dimensions: 86 x 86 mm
- Polished stainless steel

### General characteristics

#### Synergy™ - shaver sockets, cable outlets, blanking plates and cord outlets - Authentic

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.589\)](#)



#### Installation & technical data

- [F02325EN-00](#)