

CAT. N° 4 311 03

**DCX-M CHANGEOVER SWITCHE - SIZE 2 - 3P - 125 A - I-O-II**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	4,112
Weight (g)	1 961,00

**Product characteristics****Changeover switches****Size 2**

- Connection with lugs
- 3P
- Intensity : 125 A
- Handle : I - O - II

**General characteristics****DCX-M changeover switches - from 40 to 1600 A**

- Conform to IEC EN 60947-3
- Moulded case design with frame parts of non - flammable glass fibre reinforced polyester with high mechanical and electrical track resistance and with low water absorption
- Knife - type contacts with self - wiping action on the contact surfaces, providing:
  - under heavy starting currents or with short - circuit conditions, the contact pressure is increased
  - shock and vibration proof contacts
- Four breaking points per pole with two double - break contacts

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.172\)](#)
- [Selection chart \(p.174-175\)](#)
- [DCX-M changeover switches](#)