

CAT. N° 4 311 23

**DCX-M CHANGEOVER SWITCHE - SIZE 2 - 3P+N - 125 A - I-O-II**

|                           |          |
|---------------------------|----------|
| Pack (number of units)    | 1        |
| Volume (dm <sup>3</sup> ) | 4,301    |
| Weight (g)                | 2 251,00 |

**Product characteristics****Changeover switches****Size 2**

- Connection with lugs
- 3P+N
- Intensity : 125 A
- Handle : I - O - II

**General characteristics****DCX-M changeover switches - from 40 to 1600 A**

- Conform to IEC EN 60947-3
- Moulded case design with frame parts of non - flammable glass fibre reinforced polyester with high mechanical and electrical track resistance and with low water absorption
- Knife - type contacts with self - wiping action on the contact surfaces, providing:
  - under heavy starting currents or with short - circuit conditions, the contact pressure is increased
  - shock and vibration proof contacts
- Four breaking points per pole with two double - break contacts

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.172\)](#)
- [Selection chart \(p.174-175\)](#)
- [DCX-M changeover switches](#)