

CAT. N° 0 036 58



DIMMER - FOR FLUORESCENT LAMP WITH 0-10 V BALLAST - MAX. 800 VA - 2 MODULES

Pack (number of units)	1
Volume (dm ³)	0,701
Weight (g)	129,00

Product characteristics

Remote control dimmers 100 - 240 V~ - 50/60 Hz

Controlled via non-illuminated push-buttons

- Symmetrical rail mounting
- The last lighting level is stored into memory, in case of power cut or switch-off
- For fluorescent lamps with 1-10 V dimmable ballast (fl uorescent tubes and compact fluorescent lamps with separated dimmable ballast)
- Ballast power: maximum 800 VA (for 230 V~ - 50/60 Hz)
- Control current: 50 mA
- Number of modules : 2

General characteristics

Lighting management remote control dimmers

Documentation

Catalogue pages & additional information

- [Description page \(p.094\)](#)
- [Dimensions of din-rail equipment](#)
- [Light sensitive switches](#)

Environmental product profile

- [Environnemental product sheet n°A E0186A-EN](#)

Installation instructions & related documents

- [0064GS2/00](#)