

CAT. N° 4 016 76



DISTRIBUTION CABINET XL³ 125 - 1 ROW - 18 MODULES - SURFACE MOUNTING

Pack (number of units)	1
Volume (dm ³)	19,964
Weight (g)	2 367,00

Product characteristics

Surface mounting distribution cabinets

- Capacity 18 modules per row
- White RAL 9003
- Fully reversible cabinet (base, door and faceplates)
- Supplied with:
 - removable and pivoting chassis with rails fitted. Rails can be individually removed for easy cabling on site
 - removable cable entry plate (top and bottom)
 - removable faceplates (for each row)
 - IP 2X screw terminal blocks for neutral and earth
 - blanking plates (5 modules, separable per module or 1/2 module) 1 sheet of self-adhesive labels for circuit identification (marking per module)
- Spacing between rails 150 mm
- Adjustable rail (2-position) for fitting modular equipment or DPX³ 160 moulded case circuit breakers
- Can be fitted with perforated plates and solid faceplates for mounting non-modular products (2, 3 to 4-row cabinets)
- Doors to be ordered separately
- Number of rows : 1
- Number of modules : 18
- Height : 300 mm
- Width : 450 mm
- Depth : 128 mm

General characteristics

Surface mounting cabinets XL³ 125 - from 18 to 72 modules

- IP 40 - IK 09 with door
- IP 30 - IK 08 without door
- Class II
- Self-extinguishing: resistance to incandescent wire 650 °C
- Conform to IEC 60670-24
- Allows to achieve assemblies conform to IEC 61439-3

Documentation

Catalogue pages & additional information

- [Description page \(p.222\)](#)
- [Technical page \(p.223\)](#)

Installation & technical data

- [F01233EN/05](#)

Installation instructions & related documents

- [LE07398AA_01](#)

Agreements & certificates of conformity

- [OC / CB - 654749](#)
- [OC / CB - 675993](#)