

CAT. N° 6 381 60



## DISTRIBUTION MINI-TRUNKING 50 X 20 MM - WITHOUT CENTRAL PARTITION - 2 M LENGTH

Pack (number of metres)	40
Volume (dm <sup>3</sup> )	48,531
Weight (g)	9 400,00

### Product characteristics

#### 50 x 20 and 60 x 20 mm mini-trunking

- Conform to EN 50085-2-1

#### Without central partition

- 50 x 20
- Length 2 m
- Supplied in 20 or 16 lengths of 2 metres

### General characteristics

#### DLP-S distribution mini-trunking 32 x 16 / 40 x 16 / 50 x 20 / 60 x 20 and 40 x 40

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.805\)](#)
- [Description page \(p.807\)](#)
- [DLP-S distribution mini-trunking wiring capacity chart and installation](#)

#### Agreements & certificates of conformity

- NF 004 - NF004\_1002

#### Installation & technical data

- [F01197EN/02](#)

#### Environmental product profile

- [Environnemental product sheet n°6 E7113A-EN](#)