

CAT. N° 0 048 67



DISTRIBUTION TERMINAL - 160 A - 6 OUPUTS 25 MM² FLEXIBLE

Pack (number of units)	1
Volume (dm ³)	0,162
Weight (g)	105,00

Product characteristics

Distribution terminals

- 160 A - 6 outputs 25 mm² flexible - I_{sc} peak 30 kA
- Can be fitted directly onto downstream terminal of Vistop 100/160 A

General characteristics

Modular distribution blocks 40 to 250 A

- Standard distribution
- Connection with or without Starfix ferrules
- Self-extinguishing, according to EN 60695-2-11: 960 °C on active part supports

Documentation

Catalogue pages & additional information

- [Selection chart \(p.198\)](#)
- [Description page \(p.201\)](#)
- [Modular distribution blocks](#)