

CAT. N° 0 126 25



## DOMESTIC CARTRIDGE FUSE - CYLINDRICAL TYPE 10.3 X 31.5 - 25 A - WITHOUT INDICATOR

Pack (number of units)	10
Volume (dm <sup>3</sup> )	0,045
Weight (g)	63,00

### Product characteristics

#### Cylindrical

10.3 x 31.5

- Rating : 25 Amps
- Voltage ~ : 400 Volts
- Rupture capacity Copper : 20000 Amps
- Protected section : 4 mm<sup>2</sup>
- Color Indication : Blue

### General characteristics

#### Domestic cartridge fuses

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.082\)](#)
- [Dimensions of din-rail equipment](#)



#### Agreements & certificates of conformity

- [NF - 656079/A1](#)