

CAT. N° 0 123 02



## DOMESTIC CARTRIDGE FUSE - CYLINDRICAL TYPE GG 8 X 32 - 2 A - WITHOUT INDICATOR

Pack (number of units)	10
Volume (dm <sup>3</sup> )	0,036
Weight (g)	45,00

### Product characteristics

#### Cylindrical type gG

- Conform to EN 60269-1, IEC 60269-1 and 2

#### 8 x 32 (previously 8.5 x 31.5)

- Without indicator
- Rating : 2 Amps
- Voltage ~ : 400 Volts
- Rupture capacity : 20000 Amps

### General characteristics

#### HRC cartridge fuses

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)

#### Installation & technical data

- [F00192EN-08](#)