

CAT. N° 8 334 12



DOUBLE POLE SWITCH SYNERGY - BLUE LED POWER INDICATOR -20 A -250 V~ -AUTHENTIC GLOSSY GOLD

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,462 |
| Weight (g) | 142,00 |

Product characteristics

Double pole switches 20 A - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 25 mm deep
- Use cord outlet accessory Cat.No 7 300 53 for external cord outlet
- Nominal plate dimensions: 86 x 86 mm

DP switches + blue LED power indicator

- Glossy gold

General characteristics

Synergy™ - fan switch and double pole switches - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.586\)](#)

Agreements & certificates of conformity

- [ASTA - 782](#)
- [QC / CB - FR 686293A/A1](#)

Installation & technical data

- [F02252EN-00](#)