

CAT. N° 8 332 23



DOUBLE POLE SWITCH SYNERGY -1 GANG -BLUE LED -20 A -250 V~ - AUTHENTIC POLISHED STAINLESS STEEL

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Double pole switches 45 A - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 45 mm deep

1 gang switches + blue LED power indicator

- Nominal plate dimensions: 86 x 86 mm
- Polished stainless steel

General characteristics

Synergy™ - fan switch and double pole switches - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.586\)](#)

Agreements & certificates of conformity

- [OC / CB - 60055284A/M1/A1](#)
- [ASTA - 783](#)

Installation & technical data

- [F02253EN-00](#)