

CAT. N° 7 530 49



## DOUBLE RJ 45 CATEGORY 6 A DATA SOCKET VALENA IN'MATIC - STP

Pack (number of units)	5
Volume (dm <sup>3</sup> )	1,912
Weight (g)	651,00

### Product characteristics

#### Data sockets Cat. 6 A

- With LCS2 connector with fast connection thanks to integrated crimping
- Take AWG 22 single-core cables up to AWG 26 and AWG multicore cables
- Contacts marked with dual colour code and wiring schemes 568 A and 568 B
- Conform to standards ISO/IEC 11801 Ed. 2.0, amendment 2, EN 50173-1 and TIA/EIA 568 C2

#### Double RJ 45 sockets Cat. 6 A

- STP

### General characteristics

#### Valena™ IN'MATIC mechanisms - data, fibre optic and telephone sockets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.500\)](#)
- [Selection chart \(p.510\)](#)
- [Selection chart \(p.514\)](#)

#### Installation & technical data

- [F02127EN-00](#)

#### Installation instructions & related documents

- [LE07421AB](#)