

CAT. N° 0 415 33



## ELECTROMECHANICAL SIREN - IP30 - IK05 - 24 V= - 12 W- 516 MA

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,315
Weight (g)	241,00

### Product characteristics

#### Electromechanical sirens IP 30 - IK 05

- Supplied with screws for semi-flush mounting

#### D.C. current

- Voltage : 24 V=
- Power : 12 W
- Consumption : 516 mA
- Average acoustic output at 1 m : 100 dB
- Weight : 0.2 kg
- Max. continuous rating : 200 hr

### General characteristics

#### Electromechanical and electronic sirens

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.394\)](#)
- [Technical page \(p.395a\)](#)

#### Environmental product profile

- [Environnemental product sheet n°4 E0061A-FR](#)

#### Installation instructions & related documents

- [4065212/04](#)