

REF . 0 660 00


**EMERGENCY LIGHTING LUMINAIRE S8 - 8 WNON-MAINTAINED - 1H - 140 LM**


|                                     |        |
|-------------------------------------|--------|
| Emballage (nombre number of units ) | 1      |
| Volume (dm <sup>3</sup> )           | 3,007  |
| Poids (g)                           | 914,00 |

**Caractéristiques du produit**
**8 W fluorescent non-maintained, maintained and combined units**


- Certified to IEC 60598-2-22 and EN 60598-2-22 standards
- IP 42 - Class II
- Power supply: 230 V +/- 10% - 50/60 Hz
- Lamp and emergency operation test with a push-button
- Ni-Cd batteries
- Recharge time: 24 hours
- High capacity screw terminals: 2 x 2.5 mm<sup>2</sup>
- Charge monitor with a green LED

**1 h duration - 140 lm**

- Non-maintained - 140 lm - 1h (1 x 8 W)

**Caractéristiques générales**
**S8 - indoor standard self-contained emergency lighting luminaires 8 W fluorescent - BS compliant**

- Can be equipped with metallic protection grid Cat.No 0 626 91

**Documentation associée**
 **Catalogue pages & additional information**

- [Selection chart \(p.679\)](#)
- [Description page \(p.687\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)

 **Agreements & certificates of conformity**

- [OC / CB - ES1953-M3](#)

 **Installation instructions & related documents**

- [LE08468AA](#)