

CAT. N° 4 149 47



## ENERGY MANAGEMENT MULTI-SUPPORT WEB SERVER FOR 10 MODULES BUS ADDRESSES OR 10 PULSE MODULES

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,716  |
| Weight (g)                | 174,00 |

### Product characteristics

#### Energy management multi-support web servers

- Allow remote configuration, test, control and visualization, via a web browser on PCs, smartphones, web viewers, tablet computers, of data collected from: protection devices (DX<sup>3</sup> add-on modules with integrated measurement control unit, DPX<sup>3</sup> and DMX<sup>3</sup>), EMDX<sup>3</sup> electricity meters and multi-function measuring units, CX<sup>3</sup> energy management system and Green'up charging stations for electric vehicles

#### Rail mounting

- Direct IP connection
- Power supply: 9 to 28 V= with the help of a single-phase switching mode power supply Cat.No 1 467 21 to be ordered separately
- For 10 Modbus addresses or 10 pulse modules
- Number of modules : 4

### General characteristics

#### Power supervision system - remote control, monitoring and measurement

- With the Legrand Power supervision system, circuit breakers are integrated in a supervision system
- You can therefore check the status of the circuit breakers, measure the electrical values and control the circuit breakers remotely
- MODBUS protocol

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.101\)](#)
- [Description page \(p.103\)](#)
- [Description page \(p.105\)](#)
- [Technical page \(p.108-109\)](#)

#### Installation & technical data

- [F02466EN-02](#)
- [PARAMETER TABLE-EN](#)
- [USER MANUAL-PC](#)
- [USER GUIDE-SP](#)

#### Installation instructions & related documents

- [LE10102AB](#)

#### Softwares

- [Legrand Energy Management Web Server Software](#)