


CAT. N° 0 160 40



HRC BLADE TYPE CARTRIDGE FUSE - CYLINDRICAL TYPE AM 22 X 58 - 32 A - W INDICATOR

Pack (number of units)	3
Volume (dm ³)	0,693
Weight (g)	601,00

Product characteristics

Type aM (motor rated)

- Conform to EN 60269-1, IEC 60269-1, 2 and VDE 0636-1
- Fully insulated end plate and handle lugs

Size 00

- With indicator
- Rating : 80 Amps
- Voltage ~ : 500 Volts
- Breaking capacity : 120000 Amps

General characteristics

HRC blade type cartridge fuses - gG/gL and aM types

Documentation



Catalogue pages & additional information

- [Description page \(p.180\)](#)
- [Blade cartridge fuses gG and aM types](#)



Installation & technical data

- [F00190EN/06](#)