

REF . 0 120 10



HRC CARTRIDGE FUSE - CYLINDRICAL A TYP EM 8.5 X 31.5 - 10 A - WITHOUT INDICATOR



Emballage (nombre number of units)	10
Volume (dm ³)	0,036
Poids (g)	45,00

Caractéristiques du produit

Cylindrical type aM (motor rated)

- Conform to EN 60269-1, IEC 60269-1 and 2

8 x 32 (previously 8.5 x 31.5)

- Without indicator
- Rating : 10 Amps
- Voltage ~ : 400 Volts
- Rupture capacity : 20000 Amps

Caractéristiques générales

HRC cartridge fuses

Documentation associée



Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)



Installation & technical data

- [F00188EN/06](#)