

CAT. N° 0 130 08



HRC CARTRIDGE FUSE - CYLINDRICAL TYPE AM 10 X 38 - 8 A - WITHOUT INDICATOR

Pack (number of units)	10
Volume (dm ³)	0,057
Weight (g)	76,00

Product characteristics

Cylindrical type aM (motor rated)

- Conform to EN 60269-1, IEC 60269-1 and 2

10 x 38 HRC

- Without indicator
- Rating : 8 Amps
- Voltage ~ : 500 Volts
- Rupture capacity : 100000 Amps

General characteristics

HRC cartridge fuses

Documentation



Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)



Installation & technical data

- [F00188EN/06](#)