

CAT. N° 0 141 02



## HRC CARTRIDGE FUSE - CYLINDRICAL TYPE AM 14 X 51 - 2 A - WITH INDICATOR

Pack (number of units)	10
Volume (dm <sup>3</sup> )	0,161
Weight (g)	211,00

### Product characteristics

#### Cylindrical type aM (motor rated)

- Conform to EN 60269-1, IEC 60269-1 and 2

#### 14 x 51 HRC

- With striker
- Rating : 2 Amps
- Voltage ~ : 500 Volts
- Rupture capacity : 100000 Amps

### General characteristics

#### HRC cartridge fuses

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)

#### Installation & technical data

- [F00188EN/06](#)