

CAT. N° 0 778 21

**INTERMEDIATE SWITCH SOLIROC - 10 AX 250 V~ - IP55**

Pack (number of units)	1
Volume (dm ³)	0,68
Weight (g)	201,00

Product characteristics**Switches 10 AX - 250 V~**

- Intermediate switch

General characteristics**Soliroc™ - control mechanisms IK 10**

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied with cover plates, to be equipped with support frames and plates

Documentation **Catalogue pages & additional information**

- [Description page \(p.610\)](#)

 **Agreements & certificates of conformity**

- [NF - NF012_1023](#)
- [OC / CB - FR_707077](#)

 **Installation & technical data**

- [F00997EN-04](#)